

TECHSPEC® C-Mount Achromat Pair 1:2 with 75 and 150mm Focal Lengths



Stock #87-191 [CONTACT US](#)

- 1 + **£314.50**

ADD TO CART

Qty 1-5
£314.50
Qty 6+
£251.60
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
40-20

Working f#:
f/7.5 - f/188

Coating:
VS 0° (425-675nm)

Coating Specification:

R _{avg} ≤0.4% @ 425 - 675nm
Aperture (mm): 0.8 - 20
Effective Focal Length EFL A (mm): 75.0
Effective Focal Length EFL B (mm): 150.0
Housing Diameter (mm): 38.00
Housing Length (mm): 45.9
Magnification: 1:2
Object Distance (mm): 60.00
Image Distance (mm): 135.00
Type: Relay Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View