

TECHSPEC® C-Mount Extension Tube Kit



Stock **#54-668** **4 In Stock**

- 1 + £293.⁶⁰

ADD TO CART

Volume Pricing	
Qty 1-4	£293.60 each
Qty 5-9	£258.96 each
Qty 10-25	£238.48 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

C-Mount Kit **Type:**

Extension Tube (Fixed) **Function:**

Contents of Kit:

5mm: [#54-628](#), 10mm: [#54-629](#), 15mm: [#54-630](#),
50mm: [#54-632](#), 100mm: [#54-633](#)

Physical & Mechanical Properties

22.0 **Clear Aperture CA (mm):**

30.0 **Outer Diameter (mm):**

Threading & Mounting

C-Mount **Thread Type:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 235:**

Product Details

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.

Technical Information

