

TECHSPEC[®] C-Mount Extension Tube Kit



Stock **#54-668** 2 In Stock

-

1

+

£293^{.60}

ADD TO CART

Volume Pricing	
Qty 1-4	£293.60 each
Qty 5-9	£258.96 each
Qty 10-25	£238.48 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

C-Mbunt Kit

Type:

Contents of Kit: 5mm: #54-628 , 10mm: #54-629 , 15mm: #54-630 , 50mm: #54-632 , 100mm: #54-633	
Extension Tube (Fixed)	Function:
Physical & Mechanical Properties	
30.0	Outer Diameter (mm):
22.0	Clear Aperture CA (mm):
Threading & Mounting	
C-Mount	Thread Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

PRODUCT DETAILS

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.

TECHNICAL INFORMATION

C-Mount Dimensions

1-32 C-Mount
Female Thread

