

**TECHSPEC® C-Mount Male Aperture Cap**



C-Mount Male Aperture Cap

Stock #58-199 **5 In Stock**

⊖ 1 ⊕ £13<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	£13.80 each
Qty 10+	£12.32 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Tube Cap **Function:**

**Physical & Mechanical Properties**

31.70 **Diameter (mm):**

3.0 **Total Length (mm):**

Thickness (mm):

12.50

## Threading & Mounting

Thread Type:

C-Mount

## Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

## Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

**Note:** #11-139 and #11-142 each include one S-Mount Aperture Cap (#11-137)

## Technical Information

