

[See all 15 Products in Family](#)

CM3-U3-31S4C-CS 1/1.8" Chameleon®3 Color Camera

See More by [Teledyne FLIR](#)



USB 3.0 FLIR Chameleon Camera



Stock **#36-076** **3 In Stock**

- 1 + £460⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | £460.00 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Color

Spectrum:

General

Color Camera

Type:

CM3-U3-31S4C-CS

Model Number:

FLIR **Manufacturer:**

Chameleon@3 **Camera Series:**

Physical & Mechanical Properties

Dimensions (mm):
44 x 35 x 22.1 (excludes connectors and lens mount)

Weight (g):
54.9

Housing:
Full

Sensor

Image Buffer:
16MB

Sensor Format:
1/1.8"

Resolution (Megapixels):
3.20

Frame Rate (fps):
55.00

Pixels (H x V):
2,048 x 1,536

Pixel Size, H x V (µm):
3.45 x 3.45

Sensing Area, H x V (mm):
7.07 x 5.3

Imaging Sensor:
Sony IMX265

Type of Sensor:
Progressive Scan CMOS

Shutter Type:
Global

Pixel Depth:
12 bit

Exposure Time:
11µs - 32s

Dynamic Range (dB):
71.38

Machine Vision Standard:
USB3 Vision v1.0

Electrical

Power Consumption (W):
Not Specified

Hardware & Interface Connectivity

Interface:
USB 3.0

Connector:
USB 3.1 Gen 1, Micro-B with Screw Locks

Power Supply:
Power over USB or via GPIO

GPIOs:
1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports

Synchronization:
Hardware Trigger (GPIO)

Interface Port Orientation:
Side Panel

GPIO Connector Type:
9-pin JST

Threading & Mounting

Mount:
CS-Mount

Mounting Threads:
¼-20 with Tripod Mount Adapter [#88-210](#)

Environmental & Durability Factors

Operating Temperature (°C):
0 to +45

Storage Temperature (°C):
-30 to +60

Regulatory Compliance

[Exempt](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Contains SVHC\(s\)](#)

Reach 240:

Product Details

- USB3 Connectivity
- Lightweight Construction
- Compact Design



Teledyne
Authorized
Distributor

Teledyne FLIR IIS Chameleon®3: Easy integration with USB3

Compact USB3 cameras

The **Chameleon®3** camera line combines popular CCD and CMOS image sensors with the ease of use of USB 3.0, with a compact form factor and camera sensor resolutions ranging from 1.3 MP to 5.0 MP.

These cameras feature a compact 44 x 35 x 19.5mm lightweight metal case designed for reliability. They offer multiple mounting points and a locking USB 3.0 connection. The camera includes an on-camera frame buffer for image retransmission and an optoisolated GPIO with a locking connection.

Features

- Compact form factor
- On-camera image processing: color interpolation, gamma, & LUT
- Data interface: USB3
- 16 MByte frame buffer
- LED Status indicator
- Spinnaker SDK and FlyCapture interfaces

Applications

- Life science instrumentation
- Factory automation
- Biometrics kiosk solutions
- Ophthalmoscopy
- 3D scanning
- Automated optical inspection