

## Coarse Movement, 1/4-20, Rack & Pinion



Rack and Pinion Movement

Stock #54-793 **10 In Stock**

⊖ 1 ⊕ £412<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	£412.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Rack and Pinion Mount **Type:**

1/4-20 Stud **Note:**

Coarse Movement **Type of Adjustment:**

### Physical & Mechanical Properties

**Dimensions (mm):**

Rack and Pinion Block: 50 H x 30 W x 50 L

35 (+23/-12) in Y **Travel (mm):**

25.5 **Travel Per Knob Rotation (mm):**

2.00 **Load Capacity (kg):**

Linear (Y) **Type of Movement:**

51.00 **Optical Centerline from Post (mm):**

## Threading & Mounting

**Mounting Post Hole and Thread:**  
3/4" Diameter Post  
1/4-20 Tapped Hole

## Regulatory Compliance

**RoHS 2015:**  
[Exempt](#)

**Reach 224:**  
[Contains SVHC\(s\)](#)

**Certificate of Conformance:**  
[View](#)

## Product Details

- Coarse or Fine Motion Available
- Thru Holes for Integrating Lenses
- 1/4-20 Stud for Mounting Cameras
- [Imaging System Bases](#), [Stainless Steel Posts](#), and [Accessories](#) also Available

Rack and Pinion Focusing Mounts for Imaging Systems add additional focus ability to imaging systems. Thru Holes are ideal for use with [TECHSPEC® VZM™ Zoom Imaging Lenses](#) or other imaging lenses. Rack and Pinion Movement with 1/4-20 stud can be used with any compatible camera or imaging lens. Rack and Pinion Focusing Mounts for Imaging Systems are offered with either coarse or fine motion. [Imaging System Bases](#), [Stainless Steel Posts](#), and [Accessories](#) are also available.