

Coherent® OBIS™ LX SF 1447430 | 660nm LX SF 35mW Single Frequency Laser

See More by [Coherent®](#)



Stock #18-724 3-4 DAYS

- 1 + **£3,710.25**

ADD TO CART

Qty 1+
£3,710.25

Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Operating Temperature (°C):
+10 to +50

Output Power (mW):
35

Polarization:
100:1 (minimum)

Power Stability (%):
<1

Spatial Mode:

TEM₀₀
Wavelength (nm): 660.00 ±1
Mode Quality, M²: ≤1.4
Warm-Up Time (minutes): <5
Pointing Stability (μrad/°C): <5
Beam Diameter Tolerance (mm): ±0.2
Pointing Stability (μrad): <30
RMS Noise: ≤0.05% (20Hz to 20MHz)
Beam Diameter (mm): 1.1
Spectral Line Width (MHz): 300
Manufacturer: Coherent®
Output Type: Free Space
Type of Laser: Diode
Beam Divergence (mrad): Full-Angle: <1.5
Laser Class - CDRH: IIIb
Color: Red
Model Number: 1447430
Peak-to-Peak Noise: <0.5% (20Hz to 20kHz)
Spectral Line Width (pm): 1.5 (maximum)

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View