

Dark Red M40.5 x 0.50 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-662 3-4 DAYS

⊖

1

⊕

£130.05

ADD TO CART

Qty 1-9

£130.05

Qty 10+

£123.84

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Blocking Wavelength Range (nm):
200-600, 760-125

Clear Aperture CA (mm):
35.50

Coating:
Hard Coated

Filter Thread: M40.5 x0.50
Color: Dark Red
Center Wavelength CWL (nm): 660.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 60.00 ±10
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 42.50
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View
