

TECHSPEC[®] 65mm Sq, 15kg Load Capacity, 25mm Travel, Metric Dovetail Stage



#16-713: Dovetail Stage, 65mm SQ, English



Stock **#16-716** 3 In Stock

-

1

+

£169⁶⁰

ADD TO CART

Volume Pricing	
Qty 1-9	£169.60 each
Qty 10+	£149.44 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
	Type:
Metric	
Included Hardware:	
4XM6 x 1.0, 10mmL Socket Head Cap Screws; 1X 3mm Allen Wrench; 1X2.5mm Allen Wrench	

Physical & Mechanical Properties

Linear (X)	Type of Movement:
Dovetail	Guide System:
Center Drive	Drive Orientation:
65 x 65	Stage Size (mm):
25	Travel (mm):
0.98	Travel (inches):
Matte Black Finish Brass	Construction:
0.5	Leadscrew Pitch (mm):
15	Load Capacity (kg):
2.56 x 2.56	Stage Size (inches):

Hardware & Interface Connectivity

Lead Screw	Type of Drive:
------------	----------------

Threading & Mounting

Mounting Threads:
(9) M6 x 1, (4) M3 x 0.5, (8) M2 x 0.4

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Product Details

- Compact Overall Size for System Integration
- Brass Construction for High Stiffness and up to 15kg Load Capacity
- Compatible with All TECHSPEC® Stages

TECHSPEC® High Load Capacity Dovetail Stages are a compact, cost-effective solution for linear adjustment within an optical system. These stages feature high stiffness brass construction and a hex driven movement, allowing for a low profile and compact overall size with 5, 10, and 15kg high load capacity options. The absence of tension springs and the included external plate lock ensure resistance to vibration and increase stability. TECHSPEC High Load Capacity Dovetail Stages are ideal for imaging and laser optics systems that require low profile integrated linear adjustments in demanding environments. These stages feature bolt patterns that are compatible with all TECHSPEC and comparable metric and English stages.

Technical Information



