

[See all 4 Products in Family](#)

Dual Axis Linear Scale Micrometer on Opal Glass w/ NIST Cert



Stock **#59-277** [CONTACT US](#)

- 1 + £1,040.⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-4 | £1,040.00 each |
| Qty 5+ | £988.48 each |
| Need More? | Request Quote |

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Yes **NIST Certification:**

Physical & Mechanical Properties

Metric: 25µm
English: 1 mil (0.001") **Scale Divisions:**

25.4 x 76.2 **Dimensions (mm):**

Thickness (mm):
1.50 ±0.100

Dimensional Tolerance (mm):
±0.100

Optical Properties

Chrome on Opal Glass Substrate:

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 235:

Product Details

- Dual Axis Design
- English and Metric Scales
- NIST Certified Version Available

Our Linear Scale Stage Micrometer is designed to accurately calibrate machine vision systems simultaneously in the X- and Y- axes. This allows calibration without rotation, and without compensation for camera aspect ratios. Micrometer features two scales – a metric scale featuring 25µm divisions, and an English scale featuring 1 mil (0.001") divisions. Target is chrome on glass or chrome on opal.

Technical Information

