

[See all 4 Products in Family](#)

## Dual Axis Linear Scale Micrometer w/ NIST Certificate



Stock #59-276 **2 In Stock**

£928.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	£928.00 each
Qty 5+	£882.32 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Yes **NIST Certification:**

### Physical & Mechanical Properties

Metric: 25µm  
English: 1 mil (0.001") **Scale Divisions:**

25.4 x 76.2 **Dimensions (mm):**

Thickness (mm):  
1.50 ±0.100

Dimensional Tolerance (mm):  
±0.100

## Optical Properties

Chrome on Glass      Substrate: □

60-40      Surface Quality:

## Regulatory Compliance

[Compliant](#)      RoHS 2015:

[View](#)      Certificate of Conformance:

[Compliant](#)      Reach 235:

## Product Details

- Dual Axis Design
- English and Metric Scales
- NIST Certified Version Available

Our Linear Scale Stage Micrometer is designed to accurately calibrate machine vision systems simultaneously in the X- and Y- axes. This allows calibration without rotation, and without compensation for camera aspect ratios. Micrometer features two scales – a metric scale featuring 25µm divisions, and an English scale featuring 1 mil (0.001") divisions. Target is chrome on glass or chrome on opal.

## Technical Information

