

**TECHSPEC® Elliptical Mirror 12.7mm Minor Axis Protected Aluminum**



Stock #32-271 **20+ In Stock**

⊖ 1 ⊕ £73<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | £73.20 each                   |
| Qty 6-25       | £58.40 each                   |
| Qty 26-49      | £55.20 each                   |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Flat Mirror **Type:**

Flatness specification is Peak to Valley **Note:**

**Physical & Mechanical Properties**

±0.020 **Thickness Tolerance (inches):**



|   |       |        |       |         |         |         |         |         |         |
|---|-------|--------|-------|---------|---------|---------|---------|---------|---------|
| B | 12.70 | 17.96  | 3.81  | #32-270 | #32-271 | #43-573 | #32-272 | #32-273 | #89-454 |
| B | 22.23 | 31.42  | 6.35  | #32-093 | #30-836 | #43-574 | #32-131 | #32-085 | #89-455 |
| B | 26.97 | 38.15  | 6.35  | #32-094 | #30-837 | #43-575 | #32-132 | #32-086 | #89-456 |
| A | 31.75 | 44.91  | 9.53  | #32-095 | #30-205 | #43-576 | #32-133 | #32-087 | #89-457 |
| A | 38.10 | 53.87  | 9.53  | #32-096 | #30-258 | #43-577 | #32-134 | #32-088 | #89-458 |
| A | 47.63 | 67.36  | 11.68 | #32-097 | #30-840 | #43-578 | #32-135 | #32-089 | #89-459 |
| B | 57.15 | 80.82  | 15.88 | #32-098 | #41-131 | #43-579 | #32-136 | #32-090 | #89-460 |
| B | 66.68 | 94.28  | 15.88 | #32-099 | #42-583 | #43-580 | #32-137 | #32-091 | #89-461 |
| B | 76.20 | 107.77 | 19.05 | #32-100 | #42-584 | #43-581 | #32-138 | #32-092 | #89-462 |

