

English Post Pivot Base



Stock #53-355 **20+ In Stock**

⊖ 1 ⊕ £18⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-9	£18.40 each
Qty 10+	£16.48 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

English **Type:**

Includes 1/4-20 Cap Screws **Note:**

English Type (1/4-20) **Compatible Post Holder:**

Physical & Mechanical Properties

47.80	Length (mm):
19.10	Width (mm):
9.50	Thickness (mm):
Black Anodized Aluminum	Construction:

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- Slot Adjustment Range of 1.00"

The narrow slotted mounting base is used for the positioning of 0.5" dia. stainless steel posts and post holder assemblies. The post/post holder is attached to the base via a counterbored clearance hole with a 1/4-20 socket screw. The base is held in place with another socket screw in the slot. The slot length allows the post to be centered at the mid-point laterally or at 45° on a 1" center hole breadboard. Anodized aluminum.

Technical Information

