

1/4-20 Thread Mount, X-Y-Z Rack & Pinion



#55-621

Stock **#55-621** 17 In Stock

-

1

+

£720⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£720.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Rack and Pinion Mount	Type:
1/4-20 Stud	Note:
Coarse Movement	Type of Adjustment:
Physical & Mechanical Properties	
Dimensions (mm):	

Rack and Pinion Block: 50 H x 30 W x 50 L	
35 (+23/-12) in Y, 30 in X, 32 in Z	Travel (mm):
25.5 coarse	Travel Per Knob Rotation (mm):
5.00	Load Capacity (kg):
Linear (XYZ)	Type of Movement:
80.00	Optical Centerline from Post (mm):

Threading & Mounting

Mounting Post Hole and Thread:	
3/4" Diameter Post 1/4-20 Tapped Hole	

Regulatory Compliance

Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- Coarse or Fine Motion Available
- Thru Holes for Integrating Lenses
- 1/4-20 Stud for Mounting Cameras
- Imaging System Bases, Stainless Steel Posts, and Accessories also Available

Rack and Pinion Focusing Mounts for Imaging Systems add additional focus ability to imaging systems. Thru Holes are ideal for use with [TECHSPEC® VZM™ Zoom Imaging Lenses](#) or other imaging lenses. Rack and Pinion Movement with 1/4-20 stud can be used with any compatible camera or imaging lens. Rack and Pinion Focusing Mounts for Imaging Systems are offered with either coarse or fine motion.[Imaging System Bases](#), [Stainless Steel Posts](#), and [Accessories](#) are also available.