

Hoya G530 (VIS) 12mm Dia., Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#34-435** 3-4 DAYS

-

1

+

£38.25

ADD TO CART

Qty 1-10

£38.25

Qty 11+

£34.00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.00

Center Wavelength CWL (nm):

530.00
Density (g/cm³): 3.12
Full Width-Half Max FWHM (nm): 50.00
Glass/Filter Number: Hoya G530
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Green
Surface Quality: 80-50
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.2
Type: Bandpass Filter
Wavelength: VIS
Parallelism (arcmin): ≤1
Dimensional Tolerance (mm): +0/-0.25

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View