

Germanium, 25.4mm, Uncoated, IR Right Angle Prism

See More by [ISP Optics](#)



Infrared (IR) Right Angle Prisms

Stock **#64-120** CLEARANCE CONTACT US



1



£849.96

ADD TO CART

Qty 1+

£849.96

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

Uncoated

Substrate: ☐

Germanium (Ge)

Surface Quality:

60-40

Type:

Right Angle Prism
Dimensional Tolerance (mm): ±0.25
Angle Tolerance (arcmin): ±10
Clear Aperture (%): 85.00
Length of Hypotenuse (mm): 35.90
Length of Legs (mm): 25.40
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 2000 - 14000
Wavelength Range (µm): 2 - 14
Surface Flatness (P-V): 2λ

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View