


SCHOTT GG-400, 50mm Dia., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#66-078** 3-4 DAYS

-

1

+

£74.80

ADD TO CART

Qty 1-10
£74.80
Qty 11+
£66.30
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
50.00

Cut-Off Position λ_c (nm):
400±6

Cut-On Wavelength (nm): 400.00
Density (g/cm³): 2.55
Glass/Filter Number: SCHOTT GG400
Coating: Uncoated
Color: Clear
Passband Limit 1 λ_{p1} (nm): 480.00
Spectral Transmittance t_p (%): 93.00
Stopband Limit λ_s(nm): 340.00
Surface Quality: 80-50
Transformation Temperature (°C): 537.00
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.38
Reflection Factor P_d: 0.92
Bevel: Protective as needed

Regulatory Compliance

Reach 181: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View