

Green M37 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-556 3-4 DAYS



1



£131.75

ADD TO CART

Qty 1-9

£131.75

Qty 10+

£125.21

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Blocking Wavelength Range (nm):
200-470, 600-959

Clear Aperture CA (mm):
32.50

Coating:
Hard Coated

Filter Thread: M37 x0.75
Color: Green
Center Wavelength CWL (nm): 525.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 80.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 39.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View