

High Output Cylindrical Type Spot Light HLV3-22BL-4C



Stock #21-867 3-4 DAYS

-

1

+

£609.45

ADD TO CART

Qty 1+
£609.45

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:
Blue

Model Number:
HLV3-22BL-4C

Dimensions (mm):
Outer diameter 22 mm, Tip diameter 8 mm, Total length 61 mm

Wavelength (nm):
465.00

Weight (g):

39
Power Consumption (W): 3.8
Active Area (mm): 6
Type of Illumination: LED Illuminator
Manufacturer: CCS
Geometry: Spot Light
Maximum Input Current: 1000mA
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View

