

# Hoya L38 (380nm), 50mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-836 3-4 DAYS

⊖ 1 ⊕ **£74.80**

ADD TO CART

Qty 1-10

£74.80

Qty 11+

£66.30

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
50.00

Cut-On Wavelength (nm):  
380.00 ±5

Density (g/cm³):  
2.96

|                                                              |
|--------------------------------------------------------------|
| <div>Glass/Filter Number:<br/><a href="#">Hoya L38</a></div> |
| <div>Substrate: <div></div><br/>Colored Glass</div>          |
| <div>Coating:<br/>Uncoated</div>                             |
| <div>Color:<br/>Clear</div>                                  |
| <div>Surface Quality:<br/>60-40</div>                        |
| <div>Transformation Temperature (°C):<br/>480</div>          |
| <div>Thickness (mm):<br/>2.50</div>                          |
| <div>Thickness Tolerance (mm):<br/>±0.1</div>                |
| <div>Type:<br/>Longpass Filter</div>                         |
| <div>Wavelength:<br/>UV</div>                                |
| <div>Dimensional Tolerance (mm):<br/>±0.2</div>              |
| <div>Reflection Factor P<sub>d</sub>:<br/>0.91</div>         |
| <div>Bevel:<br/>Protective as needed</div>                   |
| <div>Δλ (nm):<br/>&lt;35</div>                               |
| <div>TH (%):<br/>&gt;85</div>                                |

Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS:<br/><a href="#">Compliant</a></div>                  |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |