

Hoya R64 (640nm), 25.4mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-882 3-4 DAYS

⊖

1

⊕

£37.40

ADD TO CART

Qty 1-10

£37.40

Qty 11+

£33.15

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40

Cut-On Wavelength (nm):
640.00 ±5

Density (g/cm³):
2.68

Glass/Filter Number: Hoya R64
Substrate: Colored Glass
Coating: Uncoated
Color: Red
Surface Quality: 60-40
Transformation Temperature (°C): 555
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed
Δλ (nm): <35
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View