

Hoya R64 (640nm), 50mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-883 3-4 DAYS

⊖

1

⊕

£74.80

ADD TO CART

Qty 1-10

£74.80

Qty 11+

£66.30

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00

Cut-On Wavelength (nm):
640.00 ±5

Density (g/cm³):
2.68

Glass/Filter Number: Hoya R64
Substrate: Colored Glass
Coating: Uncoated
Color: Red
Surface Quality: 60-40
Transformation Temperature (°C): 555
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed
Δλ (nm): <35
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View