

Hoya U360 (UV) 50.8mm Square, 1mm Thick, Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock #18-775 3-4 DAYS

⊖ 1 ⊕

£143.65

ADD TO CART

Qty 1-10

£143.65

Qty 11+

£126.65

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
50.80 x 50.80

Center Wavelength CWL (nm):

360.00
Density (g/cm³): 2.74
Full Width-Half Max FWHM (nm): 45.00
Glass/Filter Number: Hoya U360
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Black
Surface Quality: 60-40
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Wavelength: UV
Parallelism (arcmin): ≤2
Dimensional Tolerance (mm): ±0.2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View