

Hoya UV28N (280nm), 25.4mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-794 3-4 DAYS

-

1

+

£37.40

ADD TO CART

Qty 1-10

£37.40

Qty 11+

£33.15

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40

Cut-On Wavelength (nm):
280.00 ±7

Density (g/cm³):
2.61

Glass/Filter Number: Hoya UV28N
Substrate: Colored Glass
Coating: Uncoated
Color: Clear
Surface Quality: 60-40
Transformation Temperature (°C): 572
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: UV
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed
Δλ (nm): <45
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View