

Hoya UV32N (320nm), 50mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-812 3-4 DAYS

-

1

+

£74.80

ADD TO CART

Qty 1-10
£74.80

Qty 11+
£66.30

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00

Cut-On Wavelength (nm):
320.00 ±7

Density (g/cm³):
3.23

Glass/Filter Number: Hoya UV32N
Substrate: Colored Glass
Coating: Uncoated
Color: Clear
Surface Quality: 60-40
Transformation Temperature (°C): 572
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: UV
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.90
Bevel: Protective as needed
Δλ (nm): <25
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View