

Hoya UV34N (340nm), 12.5mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-815 3-4 DAYS

-

1

+

£27.20

ADD TO CART

Qty 1-10

£27.20

Qty 11+

£23.80

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50

Cut-On Wavelength (nm):
340.00 ±7

Density (g/cm³):
4.01

Glass/Filter Number: Hoya UV34N
Substrate: Colored Glass
Coating: Uncoated
Color: Clear
Surface Quality: 60-40
Transformation Temperature (°C): 447
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: UV
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.88
Bevel: Protective as needed
Δλ (nm): <35
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View