

Hoya UV36N (360nm), 12.5mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-824 3-4 DAYS

⊖

1

⊕

£27.20

ADD TO CART

Qty 1-10

£27.20

Qty 11+

£23.80

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50

Cut-On Wavelength (nm):
360.00 ±7

Density (g/cm³):
2.52

Glass/Filter Number: Hoya UV36N
Substrate: Colored Glass
Coating: Uncoated
Color: Clear
Surface Quality: 60-40
Transformation Temperature (°C): 587
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: UV
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed
Δλ (nm): <40
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View