

# Hoya UV36N (360nm), 50mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #18-828 3-4 DAYS

⊖ 1 ⊕ **£74.80**

ADD TO CART

|          |
|----------|
| Qty 1-10 |
| £74.80   |

|         |
|---------|
| Qty 11+ |
| £66.30  |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
50.00

Cut-On Wavelength (nm):  
360.00 ±7

Density (g/cm³):  
2.52

|                                                                |
|----------------------------------------------------------------|
| <div>Glass/Filter Number:<br/><a href="#">Hoya UV36N</a></div> |
| <div>Substrate: <div></div><br/>Colored Glass</div>            |
| <div>Coating:<br/>Uncoated</div>                               |
| <div>Color:<br/>Clear</div>                                    |
| <div>Surface Quality:<br/>60-40</div>                          |
| <div>Transformation Temperature (°C):<br/>587</div>            |
| <div>Thickness (mm):<br/>2.50</div>                            |
| <div>Thickness Tolerance (mm):<br/>±0.1</div>                  |
| <div>Type:<br/>Longpass Filter</div>                           |
| <div>Wavelength:<br/>UV</div>                                  |
| <div>Dimensional Tolerance (mm):<br/>±0.2</div>                |
| <div>Reflection Factor P<sub>d</sub>:<br/>0.92</div>           |
| <div>Bevel:<br/>Protective as needed</div>                     |
| <div>Δλ (nm):<br/>&lt;40</div>                                 |
| <div>TH (%):<br/>&gt;85</div>                                  |

Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS:<br/><a href="#">Compliant</a></div>                  |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |