

[See all 33 Products in Family](#)

# IDS Imaging U3-3046LE-C-HQ 1/2.9" Color USB3 Camera (Recertified 05-P)

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye LE/XLE Camera (M12, Full Housing, Front View)



Stock #24-105-RCD-05P RECERTIFIED **1 In Stock**

[Similar Cameras](#)

- 1 + £336.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	£336.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Color Spectrum:

**General**

Color Camera Type:

Model Number:

**Manufacturer:**  
IDS Imaging Development Systems

**Camera Series:**  
uEye LE

## Physical & Mechanical Properties

**Dimensions (mm):**  
47 x 46 x 25 (excludes connectors and lens mount)

**Weight (g):**  
38

**Housing:**  
Full

## Sensor

**Image Buffer:**  
Not Specified

**Sensor Format:**  
1/2.9"

**Resolution (Megapixels):**  
1.58

**Frame Rate (fps):**  
230.00

**Pixels (H x V):**  
1,456 x 1,088

**Pixel Size, H x V (µm):**  
3.45 x 3.45

**Sensing Area, H x V (mm):**  
5.03 x 3.75

**Imaging Sensor:**  
Sony IMX273

**Type of Sensor:**  
Progressive Scan CMOS

**Shutter Type:**  
Global

**Pixel Depth:**  
12 bit

**Exposure Time:**  
40µs - 2s

**Dynamic Range (dB):**  
Not Specified

**Machine Vision Standard:**  
USB3 Vision v1.1

## Electrical

**Power Consumption (W):**  
1 - 2

## Hardware & Interface Connectivity

**Interface:**  
USB 3.0

**Connector:**  
USB Type-C

**Power Supply:**  
Power over USB

**GPIOs:**  
N/A

**Synchronization:**  
Hardware Trigger (GPIO); Software Trigger

**Interface Port Orientation:**  
Back Panel (Right Angle)

**GPIO Connector Type:**  
N/A

## Threading & Mounting

**Mount:**  
S-Mount (M12 x 0.5)

**Mounting Threads:**  
1/4-20 with Tripod Mount Adapter [#16-017](#)

## Environmental & Durability Factors

**Operating Temperature (°C):**  
0 to +55

**Storage Temperature (°C):**  
-20 to +80

## Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **REACH 241:**

## Product Details

- Up to 8.0MP Resolution with Framrates up to 230fps
- Board Level Options with C/CS-Mount or S-Mount Available
- GenICam USB3 Vision Compliant

IDS Imaging uEye LE/XLE USB3.1 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for ease of software development and integration. These cameras are available in board-level or housed options with S-Mount or C/CS-Mount versions. The C/CS-Mount configurations come with a 5mm spacer to easily adapt between C-Mount and CS-Mount lenses. IDS Imaging uEye LE/XLE USB3.1 Cameras are ideal for small device construction, medical technology, robotics, and machine vision applications. With a compact design, the XLE version is suitable for integration into embedded systems whereas the LE version is suitable for small device projects.