

IDS Imaging U3-3560XCP-C-HQ 1/3" Color USB3 Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ USB3 Camera, XCP Model (Front)



Stock **#24-142** 3-4 DAYS



1



£225.25

ADD TO CART

Qty 1+

£225.25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
USB 3.0

Type:
Color Camera

Manufacturer:
IDS Imaging

Mounting Threads: ¼-20 with Tripod Mount Adapter #16-017
Image Buffer: Not Specified
Camera Family: uEye XCP
Model Number: U3-3560XCP-C-HQ
Imaging Sensor: onsemi AR0234
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/3"
Resolution (MegaPixels): 2.30
Pixels (H x V): 1,920 x 1,200
Pixel Size, H x V (µm): 3.00 x 3.00
Sensing Area, H x V (mm): 5.76 x 3.60
Frame Rate (fps): 73.00
Pixel Depth: 10 bit
Exposure Time: 18µs - 2s
Connector: USB 3.0, Micro-B
Power Supply: Power over USB
Power Consumption (W): 0.5 - 1
GPIOs: 1 Flash Output, 1 Trigger Input, 2 GPIO, 1 Voltage Output, 2 Ground, 1 USB Pwr
Synchronization: Hardware Trigger (GPIO); Software Trigger
Dimensions (mm): 29 x 29 x 17 (excludes connectors and lens mount)
Weight (g): 61
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): Not Specified
Operating Temperature (°C): 0 to +55
Storage Temperature (°C): -20 to +60
GPIO Connector Type: 8-pin Hirose (HR25)
Machine Vision Standard: USB3 Vision v1.1

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View