

[See all 102 Products in Family](#)

## IDS U3-38J1XLS-C, USB 3.0, 1/2.8" Color Board Level Camera

See More by [IDS Imaging Development Systems](#)



Pictured is an example of an IDS Board Level Camera (Front)



Stock **#78-249** **1 In Stock**

⊖ 1 ⊕ £213<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | £213.60 each                  |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

Color **Spectrum:**

### General

Color Camera **Type:**

U3-38J1XLS-C **Model Number:**

IDS Imaging Development Systems **Manufacturer:**

uEye+ XLS **Camera Series:**

### Physical & Mechanical Properties

32.5 x 32.5 x 14 (excludes connectors and lens mount) **Dimensions (mm):**

13 **Weight (g):**

Board Level **Housing:**

### Sensor

Not Specified **Image Buffer:**

1/2.8" **Sensor Format:**

8.41 **Resolution (Megapixels):**

25.10 **Frame Rate (fps):**

3,864 x 2,176 **Pixels (H x V):**

1.45 x 1.45 **Pixel Size, H x V (µm):**

5.603 x 3.155 **Sensing Area, H x V (mm):**

Sony IMX415 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Rolling **Shutter Type:**

12 bit **Pixel Depth:**

0.032ms - 1900ms **Exposure Time:**

66.00 **Dynamic Range (dB):**

USB3 Vision **Machine Vision Standard:**

### Electrical

0.5 - 1 **Power Consumption (W):**

### Hardware & Interface Connectivity

USB 3.0 **Interface:**

USB 3.0 micro-B **Connector:**

Power over USB **Power Supply:**

8-pin connector **GPIO Connector Type:**

### Threading & Mounting

S-Mount (M12 x 0.5) **Mount:**

### Environmental & Durability Factors

0 to +85 **Operating Temperature (°C):**

-20 to +80 **Storage Temperature (°C):**

---

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

---

## Product Details

- Standard (SE), Compact (CP), and Ultra Compact (XCP) Housing Options Available
- C-Mount with Large Format CMOS Sensors up to 1.1"
- Up to 20.44MP Resolution with Framerrates up to 396fps

IDS Imaging uEye CP/XCP/SE USB3 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for easy software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The XCP cameras have an ultra-compact size of 29 x 29 x 17mm and are an excellent option for price-sensitive, single-camera applications. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat-sensitive applications. IDS Imaging uEye CP/XCP/SE USB3 Cameras are ideal for manufacturing, industrial, and automation applications.

---

;