

[See all 23 Products in Family](#)

InfiniTube FM Obj PL/FD-295 WD/0.165X (not for inline use)

See More by [Infinity Photo-Optical Company](#)



InfiniTube FM-200 (1X), #58-310



Stock **#59-116** [CONTACT US](#)

⊖ 1 ⊕ £336.⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£336.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Lens Accessory **Type:**

Regulatory Compliance

Compliant **RoHS 2015:**


Product Details

- Direct to Video C-Mount for 2/3" and Smaller Sensor Cameras
- Internal Focusing

InfiniTube™ FM Systems are used to mount infinite-conjugate objectives to C-mount cameras, yielding magnifications not possible with ordinary video lenses, such as 50X magnification. The InfiniTube™ system can be configured in a variety of fashions. It can be utilized alone (InfiniTube™ #58-310 or #58-309) for applications where illumination is provided from another source such as a backlight or directional illumination. The InfiniTube™ FM Systems can also be configured for in-line illumination with attachments. The first in-line attachment (#58-313) has been designed for high performance with objectives having a magnification of 10X or below and is not suggested for use with higher magnification objectives. The second in-line attachment (#58-312) has been designed to work with increased efficiency when used with magnifications of 10X or higher, but can be utilized with all magnifications. All in-line attachments accept our [Fiber Optic Light Guides](#) with a 0.312" tip diameter.

Note: [Standard system](#) for 2/3" sensors still available.

Technical Information



System Includes	Stock No.
InfiniTube In-Line Assembly Unit	#58-311
Hitachi KP-D20B Camera	#55-837
15.1" Diagonal LCD Monitor (US version only)	#56-522
Y-C Cable (6 ft.)	#39-255
Mtutoyo/Achrovid™ Objective Adapter	#58-316
M-150 Fiber Optic Illuminator	#55-718
Fiber Optic Light Guide (48" L)	#39-367
Fiber Optic Adapter	#38-944
Standard Boom Stand	#54-120
Rack & Pinion Mounting Plate	#54-123
C-Clamp with 1/4-20 Mounting Hole	#57-788