

Laser ZX20 640nm 30mW, 45°



Stock #19-431 3-4 DAYS

-

1

+

£905.25

ADD TO CART

Qty 1-9
£905.25
Qty 10+
£814.73
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Operating Temperature (°C):
-10 to +50

Output Power (mW):
30

Power Stability (%):
±3

Wavelength (nm):

640.00
Weight (g): 90
Laser Class - IEC: 2M
Housing Length (mm): 97
Housing Diameter (mm): 20
Storage Temperature (°C): -40 to +85
Bore Sighting (mrad): <0.8
Pointing Stability (µrad/°C): <10
Modulation Frequency (kHz): 400
Style: Homogeneous Line (Fine Line)
Manufacturer: Z-Laser
Output Type: Free Space
Type of Laser: Diode
Laser Class - CDRH: II
Color: Red
Connector: 5 pins, M12
Fan Angle (°): 45.00
Focus Range: 100mm to Collimation
Input Voltage (V): 5 - 30 DC

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View