

## M35.5 x 0.5 Mounted Linear Glass Polarizing Filter



Mounted Linear Glass Polarizing Filters

Stock **#64-898** CLEARANCE 3-4 DAYS



1



£14.41

ADD TO CART

Qty 1+

£14.41

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):

31.00

Coating:

Uncoated

Diameter (mm):

37.00

Extinction Ratio:

Approx. 19:1 at 400nm

Approx. 200:1 at 500nm

≥2700:1 at 550-650nm

|                                                           |
|-----------------------------------------------------------|
| Approx. 600:1 at 700nm                                    |
| <b>Filter Thread:</b><br>M35.5 x 0.50                     |
| <b>Substrate:</b> <input type="checkbox"/><br>Float Glass |
| <b>Operating Temperature (°C):</b><br>-15 to +70          |
| <b>Polarization:</b><br>95% Efficiency                    |
| <b>Transmission (%):</b><br>Single: 30<br>Crossed: 0.15   |
| <b>Type:</b><br>Mounted Imaging Filter                    |
| <b>Construction:</b><br>Dichroic                          |
| <b>Mount Thickness (mm):</b><br>8                         |
| <b>Wavelength Range (nm):</b><br>400 - 700                |
| <b>Mount Thickness Including Threads (mm):</b><br>10      |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>REACH 201:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |