

M39 x 0.5 Mounted IR Cut-Off Filter



Stock **#49-803** 3-4 DAYS



1



£155.55

ADD TO CART

Qty 1-9

£155.55

Qty 10+

£143.06

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
33.8

Filter Thread:
M39 x 0.50

Cut-Off Wavelength (nm):
750.00

Glass/Filter Number:

[SCHOTT KG3](#)

Index of Refraction n_d :
1.52

Note:
AR Coating: Both Surfaces Multilayer Broadband AR

Outer Diameter (mm):
40.5

Substrate: ☐
[Schott KG-3](#)

Substrate Thickness (mm):
2.0

Surface Quality:
60-40

Thickness with Mount (mm):
6.4

Type:
Mounted Imaging Filter

Wavelength Range (μm):
0.3 - 2.7

Wavelength Range (nm):
300 - 2700

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)