

M39 x 0.5 Mounted UV/IR Cut-Off Filter



Stock **#49-811** 3-4 DAYS

⊖

1

⊕

£169.15

ADD TO CART

Qty 1-9
£169.15
Qty 10+
£156.06
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
33.8

Filter Thread:
M39 x 0.50

Cut-Off Wavelength (nm):
690.00

Cut-On Wavelength (nm):

390.00
Index of Refraction n_d: 1.52 Substrate, Varies by Layer
Note: AR Coating: Both Surfaces Multi-Layer
Outer Diameter (mm): 40.5
Substrate: ☐ Float Glass
Substrate Thickness (mm): 2.0
Surface Quality: 60-40
Thickness with Mount (mm): 6.4
Type: Mounted Imaging Filter

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant