

TECHSPEC[®] M40 Spacer Kit



CA Series Fixed Focal Length Lenses



Stock **#70-707** [CONTACT US](#)

-

1

+

£152^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£152.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Note:
Kit Includes: (2) [#70-702](#), (2) [#70-703](#), (1) [#70-704](#),
(1) [#70-705](#), (1) [#70-706](#)

Spacer Ring/Tube Kit	Type:
#29-261	Compatible Lens:
Physical & Mechanical Properties	
Brass	Construction:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- APS-C (27.9mm), TFL-Mount Lens or M40 Mount Lens
- Greater than 30 MegaPixels, 3.45µm Pixel Size Sensors
- High Resolution, Compact APS-C Lens (CA)
- 35mm to 100mm Focal Length

TECHSPEC® CA (Compact APS) Series Fixed Focal Length Lenses are designed for high-resolution large-format sensors. Covering the APS-C format sensors with a 28mm image circle, these lenses feature a [TFL Mount](#) or M40 Mount. TFL Mounts feature an M35 x0.75 thread with a 17.5mm flange distance, and offer the same robustness and ease of use as a C-Mount. M40 Mounts feature a M52 x0.75 thread and provide a robust, large-format mounting solution ideal for high-resolution and larger image sensors with improved mechanical stability and optical performance compared to smaller format mounts. TECHSPEC® CA Series Fixed Focal Length Lenses offer a compact size while accommodating large format sensors, making them ideal for machine vision and [factory automation](#) applications.

These lenses won the [3rd place 2020 Inspect Award](#) and the [Silver-Level 2020 VSD Innovators Award](#).