

[See all 22 Products in Family](#)

## M46 x 0.75 Machine Vision Mounted Linear Glass Polarizing Filter



Stock #21-647 **4 In Stock**

⊖ 1 ⊕ £78<sup>40</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	£78.40 each
Qty 10+	£74.40 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Mounted Imaging Filter **Type:**

### Physical & Mechanical Properties

41.00 **Clear Aperture CA (mm):**

48.00 **Diameter (mm):**

Black Anodized Aluminum

**Construction:**

## Optical Properties

Hardcoated

**Coating:**

up to 3000:1 @ ~600nm (nominal)

**Extinction Ratio:**

40-20

**Surface Quality:**

400 - 700

**Wavelength Range (nm):**

## Threading & Mounting

M46 x 0.75

**Filter Thread:**

9.6

**Mount Thickness Including Threads (mm):**

## Regulatory Compliance

[View](#)

**Certificate of Conformance:**

[Compliant](#)

**Reach 242:**

## Product Details

- Up to 3000:1 Extinction Ratio (nominal) @ ~600nm
- Mounted in a Rotating, Locking Housing
- 40-20 Surface Quality

Mounted Machine Vision Glass Linear Polarizers feature a rotatable threaded mount with a wide range of common machine vision threads from M22 to M105. A locking thumbscrew allows the polarizer to maintain its orientation in the event of vibrations or accidental movement in a system. In addition to polarizing incident unpolarized light, these linear polarizers can be used to greatly reduce specular glare and hot spots from reflective surfaces, smooth surfaces, or surfaces covered with grease, oil, or liquid. Mounted Machine Vision Glass Linear Polarizers are ideal for machine vision applications in manufacturing, industrial, and laboratory environments.