

M52 x 0.75 Mounted UV/IR Cut-Off Filter



Stock **#54-750**

3-4 DAYS

-

1

+

**£191.25**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| £191.25                       |
| Qty 10+                       |
| £176.03                       |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):

52.8

Filter Thread:

M52 x 0.75

Cut-Off Wavelength (nm):

690.00

Cut-On Wavelength (nm):

|                                                                                 |
|---------------------------------------------------------------------------------|
| 390.00                                                                          |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.52 Substrate, Varies by Layer |
| <b>Note:</b><br>AR Coating: Both Surfaces Multi-Layer                           |
| <b>Outer Diameter (mm):</b><br>54.0                                             |
| <b>Substrate:</b> <input type="checkbox"/><br>Float Glass                       |
| <b>Substrate Thickness (mm):</b><br>2.0                                         |
| <b>Surface Quality:</b><br>60-40                                                |
| <b>Thickness with Mount (mm):</b><br>7.0                                        |
| <b>Type:</b><br>Mounted Imaging Filter                                          |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |