

M58 x 0.75 Machine Vision Mounted Linear Glass Polarizing Filter



Stock #21-732 3-4 DAYS

- 1 + **£65.02**

ADD TO CART

Qty 1-9
£65.02

Qty 10+
£62.30

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
53.00

Coating:
Hardcoated

Diameter (mm):
60.00

Extinction Ratio:

up to 3000:1 @~600nm (nominal)
Filter Thread: M58 x0.75
Surface Quality: 40-20
Type: Mounted Imaging Filter
Construction: Black Anodized Aluminum
Wavelength Range (nm): 400 - 700
Mount Thickness Including Threads (mm): 10

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View