

## M58 x 0.75 Mounted IR Cut-Off Filter



Stock **#54-747** CLEARANCE CONTACT US

-

1

+

£73.06

ADD TO CART

Qty 1+

£73.06

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):  
52.8

Filter Thread:  
M58 x 0.75

Cut-Off Wavelength (nm):  
750.00

Glass/Filter Number:  
[SCHOTT KG3](#)

Index of Refraction n<sub>d</sub>:  
1.52

|                                                                   |
|-------------------------------------------------------------------|
| <b>Note:</b><br>AR Coating: Both Surfaces Multilayer Broadband AR |
| <b>Outer Diameter (mm):</b><br>60.0                               |
| <b>Substrate:</b> <a href="#">Schott KG-3</a>                     |
| <b>Substrate Thickness (mm):</b><br>2.0                           |
| <b>Surface Quality:</b><br>60-40                                  |
| <b>Thickness with Mount (mm):</b><br>7.0                          |
| <b>Type:</b><br>Mounted Imaging Filter                            |
| <b>Wavelength Range (µm):</b><br>0.3 - 2.7                        |
| <b>Wavelength Range (nm):</b><br>300 - 2700                       |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |