

## M6 x 1.0 Bumper (Package of 4), Sorbothane Bumpers



Stock #56-923 **20+ In Stock**

1 £38<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-2	£38.60 each
Qty 3+	£34.24 each
Need More?	<a href="#">Request Quote</a>

Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Metric **Type:**

Thread Type: M6 **Note:**

#### Physical & Mechanical Properties

25.40 **Thickness (mm):**

Sorbothane **Construction:**

38.10 **Diameter (mm):**

30-65 / bumper **Load Capacity (lbs):**

### Threading & Mounting

12.7 **Thread Length (mm):**

### Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[Compliant](#) **Reach 211:**

[View](#) **Certificate of Conformance:**

## Product Details

- Absorb and Dissipate Vibration
- Stabilize Equipment up to 152lbs
- English, Metric, or Universal Styles

Sorbothane® MOUNTS absorb (57% absorption efficiency) and dissipate energy (70% specific damping). The mounts reduce vibration to other components by isolating the vibrations within the material while absorbing multi-directional forces. These hemisphere mounts can stabilize equipment weighing up to 38 pounds (hemisphere mounts), 65 pounds (1/4-20 male bumper mounts), or 29.4 kg (M6 male bumper mounts). Sorbothane® MOUNTS measure 50mm dia. (top) x 26mm thick. The top side of the hemisphere is tacky, while the other side is felt. 1/4-20 or M6 male bumper mounts measure 38.1mm dia. x 25.4mm thick. The threaded screw measures 12mm long. All models have a hardness durometer value of 70. Each package contains 4 mounts.