

M67 x 0.75 Mounted Linear Glass Polarizing Filter



Mounted Linear Glass Polarizing Filters

Stock **#64-900** ☒ In Stock

-

1

+

£52.70

ADD TO CART

Qty 1-9
£52.70

Qty 10+
£49.30

Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
62.00

Coating:
Uncoated

Diameter (mm):
70.00 +0/-0.2

Extinction Ratio: Approx. 19:1 at 400nm Approx. 200:1 at 500nm ≥2700:1 at 550-650nm Approx. 600:1 at 700nm
Filter Thread: M67 x0.75
Substrate: ☐ Float Glass
Operating Temperature (°C): -15 to +70
Polarization: 95% Efficiency
Transmission (%): Single: 30 Crossed: 0.15
Type: Mounted Imaging Filter
Construction: Dichroic
Mount Thickness (mm): 9 ±0.1
Wavelength Range (nm): 400 - 700
Mount Thickness Including Threads (mm): 11

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View