

## M86 x 1.00 Mounted Linear Glass Polarizing Filter



Mounted Linear Glass Polarizing Filters

Stock **#64-902** [CONTACT US](#)



1



£123.25

ADD TO CART

Qty 1-9

£123.25

Qty 10+

£113.73

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Clear Aperture CA (mm):**  
80.00

**Coating:**  
Uncoated

**Diameter (mm):**  
90.00 +0/-0.2

|                                                                                                                                       |
|---------------------------------------------------------------------------------------------------------------------------------------|
| <div>Extinction Ratio:<br/>Approx. 19:1 at 400nm<br/>Approx. 200:1 at 500nm<br/>≥2700:1 at 550-650nm<br/>Approx. 600:1 at 700nm</div> |
| <div>Filter Thread:<br/>M86 x 1.00</div>                                                                                              |
| <div>Substrate: <input type="checkbox"/><br/>Float Glass</div>                                                                        |
| <div>Operating Temperature (°C):<br/>-15 to +70</div>                                                                                 |
| <div>Polarization:<br/>95% Efficiency</div>                                                                                           |
| <div>Transmission (%):<br/>Single: 30<br/>Crossed: 0.15</div>                                                                         |
| <div>Type:<br/>Mounted Imaging Filter</div>                                                                                           |
| <div>Construction:<br/>Dichroic</div>                                                                                                 |
| <div>Mount Thickness (mm):<br/>9 ±0.1</div>                                                                                           |
| <div>Wavelength Range (nm):<br/>400 - 700</div>                                                                                       |
| <div>Mount Thickness Including Threads (mm):<br/>11</div>                                                                             |

Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS:<br/><a href="#">Compliant</a></div>                  |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |