


Micro Line and Dot Standard Stage Micrometer



Stock **#58-606** **2 In Stock**

-

1

+

£643^{.49}

ADD TO CART

Volume Pricing	
Qty 1-4	£643.49 each
Qty 5+	£612.07 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

No

NIST Certification:

Physical & Mechanical Properties

Scale Divisions: 2µm, 3µm, 4µm, 5µm, 6µm, 7µm, 8µm, 9µm, 10µm, 25µm, 50µm, 75µm, 100µm	
Dimensions (mm): 25.4 x 76.2	
Thickness (mm): 1.50 ±0.100	
Dimensional Tolerance (mm): ±0.100	
Optical Properties	
Substrate: Chrome on Glass	
Surface Quality: 60-40	
Regulatory Compliance	
RoHS 2015: Compliant	
Certificate of Conformance: View	
Reach 235: Compliant	

PRODUCT DETAILS

- New Opal Version Available
- Calibrate Pixel Dithering
- Lines and Dot Range from 2µm to 100µm

The Micro Line and Dot Standard is designed to calibrate imaging devices performing critical measurements. The pattern features known dot and line sizes of 2µm, 3µm, 4µm, 5µm, 6µm, 7µm, 8µm, 9µm, 10µm, 25µm, 50µm, 75µm, 100µm. Calibrating with this target can limit the effects of pixel dithering in image processing algorithms. Target is chrome on glass or chrome on opal.