

Mid-IR Variable Ultrafast Pulse Stretcher, 2800 - 3600nm



Stock **#26-403** [CONTACT US](#)

- 1 + **£6,025.65**

ADD TO CART

Qty 1+
£6,025.65

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Polarization:
p

Dimensions (inches):
9 x 8 x 4

Wavelength Range (nm):
2800 - 3600

GDD Specification (fs²):
1000 to 4000

Input Beam Diameter, 1/e² (mm):
2 (maximum)

Minimum Efficiency (%):
86.40

GDD Increment (fs²):
1000

Regulatory Compliance

RoHS:
Compliant

Certificate of Conformance:
[View](#)