

Mounted M25.5 x 0.5 Threaded - Green Filter



Stock **#46-543** CLEARANCE CONTACT US

-

1

+

£23.76

ADD TO CART

Qty 1+

£23.76

Volume Pricing

[Request Quote](#)

!

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
21.5

Filter Thread:
M25.5 x 0.50

Color:
Green

Cut-Off Wavelength (nm):
550.00

Cut-On Wavelength (nm):
520.00

Glass/Filter Number: G-533
Index of Refraction n_d: 1.54
Note: AR Coating: MgF ₂
Outer Diameter (mm): 27.5
Substrate: ☐ Colored Glass
Substrate Thickness (mm): 2.0
Surface Quality: 80-50
Thickness of Compatible Optics (mm): 2.0
Thickness with Mount (mm): 5.00
Type: Mounted Imaging Filter
Type of Filter: Hoya G-533 or equivalent
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View