

Mounted M43 x 0.75 - UV Cut-Off Filter



Mounted UV Filters

Stock #54-040 **10 In Stock**

⊖ 1 ⊕ £56.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	£56.00 each
Qty 10-25	£50.40 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Mounted Imaging Filter **Type:**

Physical & Mechanical Properties

39.5 **Clear Aperture CA (mm):**

45.0 **Outer Diameter (mm):**

4.50 Thickness with Mount (mm):

2.00 ±0.2 Thickness (mm):

Optical Properties

390.00 Cut-On Wavelength (nm):

L-39 Glass/Filter Number:

Hoya L-39 Substrate:

AR Coated Coating:

Clear Color:

80-50 Surface Quality:

R_{avg} >2% @ 400 - 700nm Coating Specification:

350 - 2200 Wavelength Range (nm):

4 - 6λ Surface Flatness (P-V):

Threading & Mounting

M43 x 0.75 Filter Thread:

Environmental & Durability Factors

-15 to +70 Operating Temperature (°C):

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- Blocks UV and Transmits Visible
- Ideal as Dust or Protective Covers for Camera Sensors

Mounted UV Filters are offered with standard photographic and lens filter mount threads. These filters are ideal for applications where UV light needs to be blocked and visible light passed. The mounted clear aperture is 5mm less than the mount diameter. The maximum outer diameter is 2mm greater than the mount diameter, except for the 62mm and 72mm, which are 3mm larger. Mounted UV Filters are clear in color and non-rotatable.

Technical Information

