

Mounted M86 x 1.0 - UV Cut-Off Filter



Mounted UV Filters

Stock #64-895 CLEARANCE 3-4 DAYS

⊖

1

⊕

£84.11

ADD TO CART

Qty 1+

£84.11

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
81.0

Cut-On Wavelength (nm):
390.00

Filter Thread:
M86 x 1.00

Glass/Filter Number:
L-39

Substrate: ☐

Hoya L-39
Operating Temperature (°C): -15 to +70
Coating: Multi-coated
Color: Clear
Outer Diameter (mm): 89.0 +0/-0.2
Thickness with Mount (mm): 5.00
Surface Quality: 80-50
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.2
Type: Mounted Imaging Filter
Coating Specification: R _{avg} >2% @ 500 - 700nm
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): 4 - 6λ
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View