

[See all 10 Products in Family](#)

Nikon Type N 50ml PCB Free Immersion Oil

See More by [Nikon](#)



Stock #75-381 NEW **1 In Stock**

⊖ 1 ⊕ £40⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£40.80 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Manufacturer:
Nikon

Optical Properties

Index of Refraction (n_d):
1.518

Abbe Number (v_d):
41

Environmental & Durability Factors

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Superior UV Transmission
- High Numerical Aperture Designs
- Feature Low Auto-Fluorescence Materials

Nikon CFI Super Fluor Objectives are designed to provide superior transmission to ultraviolet applications operating down to 340nm, including for use with fluorochromes indo-1, fura-2, and fluo-3, or for photo-activation of caged compounds. Nikon CFI Super Fluor Objectives are designed using low auto-fluorescence materials along with high numerical apertures to guarantee sharp, bright fluorescence images. These microscope objectives have been optimized for improved signal-to-noise ratios at short wavelengths.

Technical Information

Dimensions (mm)						
Stock No.	Magnification	Parfocal Length	A	B	C	D
#75-345	4X	60.06	30.0	44.3	19.7	M25 x 0.75
#88-375	10X	60.06	32.0	58.9	12.0	M25 x 0.75
#88-376	20X	59.90	33.5	58.9	9.0	M25 x 0.75
#75-346	40X	60.06	32.0	59.8	8.3	M25 x 0.75

